


Art.-Nr.: 10.01.17.00139



REIB-RING SGM 70 PU-55

Technical data

Attribute	Value
Size	70
Utilization design	Magnetic gripper
Outside diameter D	68.00 mm
Internal diameter d	51.00 mm

**Design data**

Attribute	Value
Length L	8.80 mm
Outside diameter D	68.00 mm

Design data REIB-RING SGM 70 PU-55



Art.-Nr.: 10.01.17.00139



Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55.0 Shore A
Weight	11.6 g
Size	70
Operating temperature max.	100.0 °C
Material HT2: Operating temperature max. short-term up to +250 °C	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.17.00139

