




SAXM 20 ED-85 SC045

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	20.00



Tasarım verileri

Attribute	Value
Yükseklik H2	7.00 mm
Yükseklik H	16.70 mm
Kafa çapı Dk	19.5 mm
İç çap d1	15.3 mm
İç çap d	9.70 mm
Yay stroku Z	3.0 mm
Çap Ds	21.8 mm
Çap Dmax(S)	26.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SAXM 20 ED-85 SC045

Art.-Nr.: 10.01.19.00003

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 045
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Hortum çapı (tavsiye edilen) d	5.0 mm
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Emme kuvveti (-600mbar)	20.00 N
Ağırlık	2.8 g
Yanal kuvvet	15.0 N
Yanal kuvvet yağlı yüzey	20.0 N
Cilt	2.688 cm ³
Boyut	20.00
Körük Sayısı	0.0
Ürün ailesi	SAXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00003

**Veri aksesuarları sipariş edin 10.01.19.00003**

Typ	Ürün numarası
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-IG L
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-IG L
Schmalz-Konnektör-Adaptör	SC-A 045 M10-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 M12-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 M12x1.5-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 M14x1-IG L
Schmalz-Konnektör-Adaptör	SC-A 045 M14x1.5-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 M16-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 M16x1.5-AG L
Schmalz-Konnektör-Adaptör	SC-A 045 RA L
Schmalz-Konnektör-Vida	SC-S 045 FDC-L


WWW.SCHMALZ.COM/10.01.19.00003