




SAXM 30 ED-85 SC045

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	30.00



Tasarım verileri SAXM 30 ED-85 SC045

Tasarım verileri

Attribute	Value
Yükseklik H2	7.00 mm
Yükseklik H	18.00 mm
Kafa çapı Dk	19.2 mm
İç çap d1	15.6 mm
İç çap d	9.70 mm
Yay stroku Z	4.3 mm
Çap Ds	31.6 mm
Çap Dmax(S)	35.2 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.19.00004

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 045
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Hortum çapı (tavsiye edilen) d	5.0 mm
İş parçası yarıçapı dak (dışbükey)	18.0 mm
Emme kuvveti (-600mbar)	39.00 N
Ağırlık	3.2 g
Yanal kuvvet	32.0 N
Yanal kuvvet yağlı yüzey	41.0 N
Cilt	4.549 cm ³
Boyut	30.00
Körük Sayısı	0.0
Ürün ailesi	SAXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00004

**Veri aksesuarları sipariş edin 10.01.19.00004**

Typ		Ürün numarası
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-AG L	10.01.06.02818
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-IG L	10.01.06.02736
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-AG L	10.01.06.02807
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-IG L	10.01.06.02737
Schmalz-Konnektör-Adaptör	SC-A 045 M10-AG L	10.01.06.02819
Schmalz-Konnektör-Adaptör	SC-A 045 M14x1.5-AG L	10.01.06.02820
Schmalz-Konnektör-Adaptör	SC-A 045 RA L	10.01.06.02813
Schmalz-Konnektör-Vida	SC-S 045 FDC-L	10.01.06.02803

WWW.SCHMALZ.COM/10.01.19.00004