




SAXM 40 ED-85 SC045

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	40,00



Tasarım verileri

Attribute	Value
Yükseklik H2	7,00 mm
Yükseklik H	20,60 mm
Kafa çapı Dk	19,2 mm
İç çap d1	15,6 mm
İç çap d	9,70 mm
Yay stroku Z	6,9 mm
Çap Ds	41,3 mm
Çap Dmax(S)	45,4 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SAXM 40 ED-85 SC045

Art.-Nr.: 10.01.19.00005

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 045
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Hortum çapı (tavsiye edilen) d	5,0 mm
İş parçası yarıçapı dak (dışbükey)	25,0 mm
Emme kuvveti (-600mbar)	69,00 N
Ağırlık	4,30 g
Yanal kuvvet	38,0 N
Yanal kuvvet yağlı yüzey	71,0 N
Cilt	8,317 cm ³
Boyut	40,00
Körük Sayısı	0,0
Ürün ailesi	SAXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00005

**Sipariş Verisi Aksesuarlar 10.01.19.00005**

Typ		Ürün numarası
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-AG L	10.01.06.02818
Schmalz-Konnektör-Adaptör	SC-A 045 G1/4-IG L	10.01.06.02736
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-AG L	10.01.06.02807
Schmalz-Konnektör-Adaptör	SC-A 045 G3/8-IG L	10.01.06.02737
Schmalz-Konnektör-Adaptör	SC-A 045 M10-AG L	10.01.06.02819
Schmalz-Konnektör-Adaptör	SC-A 045 M14x1.5-AG L	10.01.06.02820
Schmalz-Konnektör-Adaptör	SC-A 045 RA L	10.01.06.02813
Schmalz-Konnektör-Vida	SC-S 045 FDC-L	10.01.06.02803

