




SAXM 50 ED-85 SC055

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	50,00



Tasarım verileri SAXM 50 ED-85 SC055

Tasarım verileri

Attribute	Value
Yükseklik H2	10,50 mm
Yükseklik H	25,80 mm
Kafa çapı Dk	22,2 mm
İç çap d1	27,6 mm
İç çap d	11,80 mm
Yay stroku Z	8,4 mm
Çap Ds	51,5 mm
Çap Dmax(S)	58,4 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.19.00006

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 055
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	25,0 mm
Emme kuvveti (-600mbar)	109,00 N
Ağırlık	8,10 g
Yanal kuvvet	58,0 N
Yanal kuvvet yağlı yüzey	110,0 N
Cilt	18,016 cm ³
Boyut	50,00
Körük Sayısı	0,0
Ürün ailesi	SAXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00006

**Sipariş Verisi Aksesuarlar 10.01.19.00006**

Typ		Ürün numarası
Schmalz-Konnektör-Adaptör	SC-A 055 G1/4-AG L	10.01.06.02821
Schmalz-Konnektör-Adaptör	SC-A 055 G1/4-IG L	10.01.06.02742
Schmalz-Konnektör-Adaptör	SC-A 055 G3/8-AG L	10.01.06.02809
Schmalz-Konnektör-Adaptör	SC-A 055 G3/8-IG L	10.01.06.02743
Schmalz-Konnektör-Adaptör	SC-A 055 M10-AG L	10.01.06.02822
Schmalz-Konnektör-Adaptör	SC-A 055 M14x1.5-AG L	10.01.06.02823
Schmalz-Konnektör-Adaptör	SC-A 055 RA L	10.01.06.02815
Schmalz-Konnektör-Vida	SC-S 055 FDC-L	10.01.06.02804

