




SAXM 115 ED-85 SC065



Tasarım verileri SAXM 115 ED-85 SC065

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	115,00

Tasarım verileri

Attribute	Value
Yükseklik H2	14,30 mm
Yükseklik H	42,30 mm
Kafa çapı Dk	28,9 mm
İç çap d1	39,6 mm
İç çap d	14,00 mm
Yay stroku Z	20,0 mm
Çap Ds	115,2 mm
Çap Dmax(S)	129,4 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.19.00010

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 065
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	549,00 N
Ağırlık	52,70 g
Yanal kuvvet	320,0 N
Yanal kuvvet yağlı yüzey	584,0 N
Cilt	150,051 cm ³
Boyut	115,00
Körük Sayısı	0,0
Ürün ailesi	SAXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00010

**Sipariş Verisi Aksesuarlar 10.01.19.00010**

Typ		Ürün numarası
Schmalz-Konnektör-Adaptör	SC-A 065 G1/4-AG L	10.01.06.02824
Schmalz-Konnektör-Adaptör	SC-A 065 G1/4-IG L	10.01.06.02774
Schmalz-Konnektör-Adaptör	SC-A 065 G3/8-AG L	10.01.06.02810
Schmalz-Konnektör-Adaptör	SC-A 065 G3/8-IG L	10.01.06.02648
Schmalz-Konnektör-Adaptör	SC-A 065 M10-AG L	10.01.06.02825
Schmalz-Konnektör-Adaptör	SC-A 065 M14x1.5-AG L	10.01.06.02826
Schmalz-Konnektör-Adaptör	SC-A 065 RA L	10.01.06.02817
Schmalz-Konnektör-Vida	SC-S 065 FDC-L	10.01.06.02805

