


Çan vantuz (yuvarlak)

SAX 40 ED-85 RA




Art.-Nr.: 10.01.19.00173



SAX 40 ED-85 RA

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri SAX 40 ED-85 RA

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	40.00
Körük Sayısı	0.0
Bağlantı	Dikdörtgen adaptör

Tasarım verileri

Attribute	Value
Yükseklik H	34.00 mm
Nominal çap dn	6.75 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	7.1 mm
Çap Ds	41.3 mm
Uzunluk L4	31.80 mm
Çap Dmax(S)	45.4 mm



WWW.SCHMALZ.COM/10.01.19.00173

Art.-Nr.: 10.01.19.00173

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Emme kuvveti (-600mbar)	69.00 N
Ağırlık	38.3 g
Yanal kuvvet	49.0 N
Yanal kuvvet yağlı yüzey	71.0 N
Cilt	8.500 cm ³
Boyut	40.00
Körük Sayısı	0.0
Bağlantı	Dikdörtgen adaptör
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00173

WWW.SCHMALZ.COM/10.01.19.00173