

Çan vantuz (yuvarlak)

SAX 50 ED-85 RA



Art.-Nr.: 10.01.19.00174




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	50.00
Körük Sayısı	0.0
Bağlantı	Dikdörtgen adaptör

SAX 50 ED-85 RA

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	34.30 mm
Nominal çap dn	6.75 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	8.4 mm
Çap Ds	51.5 mm
Uzunluk L4	31.80 mm
Çap Dmax(S)	58.4 mm

Tasarım verileri SAX 50 ED-85 RA



WWW.SCHMALZ.COM/10.01.19.00174

Art.-Nr.: 10.01.19.00174



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Emme kuvveti (-600mbar)	109.00 N
Ağırlık	39.5 g
Yanal kuvvet	74.0 N
Yanal kuvvet yağlı yüzey	110.0 N
Cilt	15.200 cm ³
Boyut	50.00
Körük Sayısı	0.0
Bağlantı	Dikdörtgen adaptör
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00174

