

Çan vantuz (yuvarlak)

SAX 100 ED-85 G3/8-AG




Art.-Nr.: 10.01.19.00200



SAX 100 ED-85 G3/8-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAX 100 ED-85 G3/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	100.00
Körük Sayısı	0.0
Bağlantı	G3/8"-M

Tasarım verileri

Attribute	Value
Yükseklik H	39.70 mm
Nominal çap dn	6.10 mm
Diş G1	G3/8"-M
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	17.3 mm
Çap Ds	100.1 mm
Çap Dmax(S)	111.1 mm



WWW.SCHMALZ.COM/10.01.19.00200

Art.-Nr.: 10.01.19.00200



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Emme kuvveti (-600mbar)	412.00 N
Ağırlık	56.5 g
Yanal kuvvet	284.0 N
Yanal kuvvet yağlı yüzey	414.0 N
Cilt	96.000 cm ³
Boyut	100.00
Körük Sayısı	0.0
Bağlantı	G3/8"-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00200

