


Bell suction cup (round)

SVE 53 SI-MD-55 SC080


Art.-Nr.: 10.01.19.00255



SVE 53 SI-MD-55 SC080

Technical data

Attribute	Value
Nipple family	SC 080
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	53.00



Design data

Attribute	Value
Height H2	13.00 mm
Height H	60.50 mm
Head diameter Dk	23.0 mm
Internal diameter d1	19.6 mm
Internal diameter d	16.00 mm
Diameter Ds	52.1 mm
Height H3	14.40 mm

Design data SVE 53 SI-MD-55 SC080



WWW.SCHMALZ.COM/10.01.19.00255

Bell suction cup (round)

SVE 53 SI-MD-55 SC080



Art.-Nr.: 10.01.19.00255



Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Weight	16.4 g
Size	53.00
Product family	SVE

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00255



WWW.SCHMALZ.COM/10.01.19.00255