

Çan vantuz (yuvarlak)

SVE 33 PU-55 SC040


Art.-Nr.: 10.01.19.00266



SVE 33 PU-55 SC040

Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 040
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	33.00



Tasarım verileri SVE 33 PU-55 SC040

Tasarım verileri

Attribute	Value
Yükseklik H2	4.80 mm
Yükseklik H	37.50 mm
Kafa çapı Dk	21.5 mm
İç çap d1	11.0 mm
İç çap d	7.30 mm
Çap Ds	32.1 mm
Yükseklik H3	7.00 mm



WWW.SCHMALZ.COM/10.01.19.00266

Art.-Nr.: 10.01.19.00266



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55.0 Shore A
Ağırlık	5.7 g
Boyut	33.00
Ürün ailesi	SVE

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00266



WWW.SCHMALZ.COM/10.01.19.00266