

Bell suction cup (round)

SVE 33 PU-55 SC040


Art.-Nr.: 10.01.19.00266



SVE 33 PU-55 SC040

Technical data

Attribute	Value
Nipple family	SC 040
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55.0 Shore A
Size	33.00



Design data SVE 33 PU-55 SC040

Design data

Attribute	Value
Height H2	4.80 mm
Height H	37.50 mm
Head diameter Dk	21.5 mm
Internal diameter d1	11.0 mm
Internal diameter d	7.30 mm
Diameter Ds	32.1 mm
Height H3	7.00 mm



WWW.SCHMALZ.COM/10.01.19.00266

Bell suction cup (round)

SVE 33 PU-55 SC040



Art.-Nr.: 10.01.19.00266



Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55.0 Shore A
Weight	5.7 g
Size	33.00
Product family	SVE

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00266



WWW.SCHMALZ.COM/10.01.19.00266