




SVE 33 PU-55 G3/8-AG

Bin-Picking vantuz (elastomer parça + konektör) monte edilmiş olarak teslim edilir. Montaj şunlardan oluşur:

- SVE tipi vantuz - elastomer parça
- SC tipi bağlantı elemanı

Mevcut yedek parçalar: vantuz SVE, bağlantı elemanı SC



Tasarım verileri SVE 33 PU-55 G3/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	33.00
Diş G1	G3/8"-M

Tasarım verileri

Attribute	Value
Yükseklik H	48.50 mm
Nominal çap dn	4.10 mm
Diş G1	G3/8"-M
Diş uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	19.0 mm
Çap Ds	32.1 mm

Art.-Nr.: 10.01.19.00267

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	33.00
Ürün ailesi	SVE

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00267

**Yedek parçalar için sipariş verileri 10.01.19.00267**

Typ	Ürün numarası
Çan vantuz (yuvarlak)	SVE 33 PU-55 SC040
	10.01.19.00266

WWW.SCHMALZ.COM/10.01.19.00267