

Çan vantuz (yuvarlak)

SAX 30 ED-85 M10-AG



Art.-Nr.: 10.01.19.00368




SAX 30 ED-85 M10-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	30,00
Körük Sayısı	0,0
Bağlantı	M10-M



Tasarım verileri

Attribute	Value
Yükseklik H	26,00 mm
Nominal çap dn	4,10 mm
Diş G1	M10-M
Diş uzunluğu LG1	14,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	4,5 mm
Çap Ds	31,7 mm
Çap Dmax(S)	35,2 mm

Tasarım verileri SAX 30 ED-85 M10-AG



WWW.SCHMALZ.COM/10.01.19.00368

Art.-Nr.: 10.01.19.00368



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	18,0 mm
Emme kuvveti (-600mbar)	39,00 N
Ağırlık	33,00 g
Yanal kuvvet	38,0 N
Yanal kuvvet yağlı yüzey	41,0 N
Cilt	3,200 cm ³
Boyut	30,00
Körük Sayısı	0,0
Bağlantı	M10-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00368



WWW.SCHMALZ.COM/10.01.19.00368