

Çan vantuz (yuvarlak)

SAX 30 ED-85 M16-AG



Art.-Nr.: 10.01.19.00373




SAX 30 ED-85 M16-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	30,00
Körük Sayısı	0,0
Bağlantı	M16-M



Tasarım verileri

Attribute	Value
Yükseklik H	28,00 mm
Nominal çap dn	6,10 mm
Diş G1	M16-M
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	4,5 mm
Çap Ds	31,7 mm
Çap Dmax(S)	35,2 mm

Tasarım verileri SAX 30 ED-85 M16-AG



WWW.SCHMALZ.COM/10.01.19.00373

Art.-Nr.: 10.01.19.00373

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	18,0 mm
Emme kuvveti (-600mbar)	39,00 N
Ağırlık	35,50 g
Yanal kuvvet	38,0 N
Yanal kuvvet yağlı yüzey	41,0 N
Cilt	3,200 cm ³
Boyut	30,00
Körük Sayısı	0,0
Bağlantı	M16-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00373

WWW.SCHMALZ.COM/10.01.19.00373