

Bell suction cup (round)

SAX 30 ED-85 RA



Art.-Nr.: 10.01.19.00380




Technical data

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	30.00
Number of folds	0.0
Connection	Rectangular adapter

SAX 30 ED-85 RA

Suction cup SAX, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Height H	30.70 mm
Nominal diameter dn	6.75 mm
Key width SW1	22.0 mm
Spring stroke Z	4.5 mm
Diameter Ds	31.7 mm
Length L4	31.80 mm
Diameter Dmax(S)	35.2 mm

Design data SAX 30 ED-85 RA



WWW.SCHMALZ.COM/10.01.19.00380

1

Bell suction cup (round)

SAX 30 ED-85 RA



Art.-Nr.: 10.01.19.00380



Technical data

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Workpiece radius min. (convex)	18.0 mm
Suction force (-600mbar)	39.00 N
Weight	37.30 g
Lateral force	38.0 N
Lateral force oily surface	41.0 N
Volume	3.200 cm ³
Size	30.00
Number of folds	0.0
Connection	Rectangular adapter
Product family	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

