

Art.-Nr.: 10.01.24.00038



Technical data


Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Additional function suction cup	Friction disc
Connection	G3/8-AG
Nipple material	Aluminum

SAOXM 100x40 ED-85 G3/8-AG

Bell-shaped suction cup SAOXM (elastomer part with insert including friction disc + connection element) is delivered assembled. The assembly consists of:

- Bell-shaped suction cup of type SAOXM – elastomer part, available in various dimensions
- Insert – including moulded friction disc
- Connector upper part – available with various threads
- Connector lower part

Available spare parts: suction cup SAOXM, Schmalz-Connector-Insert, Schmalz-Connector upper part (Schmalz-Connector-Adapter), Schmalz-Connector lower part (Schmalz-Connector-Screw)



Design data

Height H	37.70 mm
Nominal diameter dn	5.10 mm
Thread G1	G3/8"-M
Thread length LG1	8.0 mm
Key width SW1	19.0 mm
Spanner size SW2	5.0 mm
Spring stroke Z	7.3 mm
Suction cup width Bs	41.60 mm
Ls	101.80 mm
Key width SW3	6.0 mm
Lmax.(S)	109.00 mm
Bmax(S)	51.00 mm

Design data SAOXM 100x40 ED-85 G3/8-AG



Bell suction cup (oval)

SAOXM 100x40 ED-85 G3/8-AG



Art.-Nr.: 10.01.24.00038



Technical data

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	32.0 mm
Suction force (-600mbar)	173.00 N
Weight	76.30 g
Dimension (LxW)	100 x 40
Lateral force	135.0 N
Lateral force oily surface	156.0 N
Volume	24.000 cm ³
Product family	SAOXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.24.00038

Typ		Item number
Schmalz-Connector-Insert	SC-I 055 AR-FDC	10.01.24.00011
Bell suction cup (oval)	SAOXM 100x40 ED-85 SC055-AR	10.01.24.00003
Schmalz-Connector-Adapter	SC-A 055-AR G3/8-AG L	10.01.06.03167



WWW.SCHMALZ.COM/10.01.24.00038