



Teknik veriler


Attribute	Value
Yükseklik H	69.00 mm
Dış çap D	140.00 mm
Ek fonksiyon vakum bloğu	Sürtünme astarı
Dış hortum çapı	8.00 mm
Şekil	Ağır Hizmet

CMB-HD D140x69 RB

CMB-HD vakum bloğu monte edilmiş ve bağlantıya hazır olarak teslim edilir.

Mevcut yedek parçalar: sızdırmazlık contası, fiş konektörü

Mevcut aksesuarlar: vakum bağlantı seti, iş parçası durdurucu, manyetik tutucu, vakum jeneratörü VAGG



Tasarım verileri

Attribute	Value
Yükseklik H2	15.00 mm
Yükseklik H	69.00 mm
Dış çap D2	8.0 mm
Dış çap D	140.00 mm
Dış G1	M10-F
Delik aralığı X1	95.0 mm
Delik aralığı X2	70.0 mm
D3	58.0 mm
Dış çap D4	98.0 mm
Außendurchmesser D5	25.0 mm

Tasarım verileri CMB-HD D140x69 RB

Vakum blok metal işleme HD
CMB-HD D140x69 RB



Art.-Nr.: 10.01.27.01875



Teknik veriler

Attribute	Value
Yanal kuvvet	493.0 N
Spannkraft	1231.0 N
Tekrarlanabilirlik	± 0,03 mm

Theoretical clamping forces of the CMB-HD vacuum blocks at -0.8 bar vacuum on aluminum, dry with theoretical coefficient of friction (lateral force) of 0.4. The values given are based on calculations. These theoretical values must be verified by the user for the respective use case by means of tests.



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01875



Veri aksesuarları sipariş edin 10.01.27.01875

Typ		Artikelnummer
Vakum hortumu (metre)	VSL 8-6 PU MI-TR	10.07.09.00003
Dur	ANSG 90x40x13	10.01.27.01925
Hortum tutucu	HTR-SL-8	10.01.27.01924
Vakum dağıtıcı	VTR-STV 8/6	10.01.27.01897



Yedek parçalar için sipariş verileri 10.01.27.01875

Typ		Artikelnummer
Sızdırmazlık tapası	VRS-STEK 8x18.5	10.08.06.00013
V halkası	V-RING 108x7 V-108-A NBR	10.07.08.00694



WWW.SCHMALZ.COM/10.01.27.01875