


Art.-Nr.: 10.01.27.01883




NLS 431x276x615 AD F EIP

The separator NLS is supplied ready for connection. The electronic integration into the bus system must be carried out by the customer. A function module can be provided on request.

Technical data

Attribute	Value
Weight	15.000 kg
Function	automatic drain
Communication	EtherNet/IP
Pressure range (operating pressure) [bar]	-1.00 ... 0.50 bar
Length L	431.00 mm
Width B	276.00 mm
Height H	615.00 mm
Voltage	24V - DC
Approval	UL/CSA
Actuation	Externally controlled



Design data NLS 431x276x615 AD F EIP

Design data

Attribute	Value
Length L	431.00 mm
Width B	276.00 mm
Height H	615.00 mm



Technical data

Attribute	Value
Applications	Control via EtherNet/IP network module, function block on request

Art.-Nr.: 10.01.27.01883

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01883**Ordering Data Accessories 10.01.27.01883**

Typ		Artikelnummer
Vacuum hose (meter)	VSL 48-38 PU-DS-AS TR	10.07.09.00031
Vacuum hose (meter)	VSL 19-13 PVC-DS KL-TR	10.07.09.00016

**Ordering Data Spare Parts 10.01.27.01883**

Typ		Artikelnummer
Check valve	SVK G3/8-IG	10.01.27.01662
Proximity switch	NAEH-SCHA NO 250V	10.01.27.01851
Proximity switch	NAEH-SCHA NC 250V	10.01.27.01852
Sieve insert	SIEB-EINS 24x 41 NLS	10.01.27.01862
Silencer (round)	SD G3/8-AG 20x56 SEG	10.02.01.00905
Solenoid valve	EMVP 6 24V-DC 3/2 NC	10.05.02.00293
Solenoid valve	EMVP 7 24V-DC 5/2 NO/NC	10.05.02.00294
Pinch valve	QV G3/8-IG	10.05.06.00085
Pinch valve	QV G3/4-IG	10.05.06.00093
Sealing element	DR-10x50 NBR	10.05.06.00113
Ball valve	KVZ 8 2/2	10.05.08.00018
Vacuum/pressure switch	VSi VP10 D M12-4	10.06.02.00798
Vacuum gauge	VAM 40 V U BAR	10.07.02.00046
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002

