

Art.-Nr.: 10.01.27.01969



VAGG 10 AC3 30 MD

The vacuum unit VAGG is supplied as a product ready to connect.

Available spare parts: vacuum gauge, oil, spare parts set float, wear parts set vacuum pump, vacuum pump


Available accessories: vacuum hose

Technical data

Attribute	Value
Suction rate (max.)	10.000 m ³ /h
Reservoir volume	30.0 l

Design data

Attribute	Value
Length L	746.00 mm
Width B	360.00 mm
Height H	733.00 mm
Outside diameter D1	14.0 mm
Outside diameter D2	7.2 mm
Outside diameter D	12.00 mm



Design data VAGG 10 AC3 30 MD



Art.-Nr.: 10.01.27.01969

**Technical data**

Attribute	Value
Max. vacuum	930 mbar
Suction rate (max.)	10.000 m³/h
Function	manual drain
Current type	Three phase A.C.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01969**Ordering Data Accessories 10.01.27.01969**

Typ	Artikelnummer
Vacuum distributor	VTR-ZF 8x 1TN MAN/KVZ 10.01.27.00126

**Ordering Data Spare Parts 10.01.27.01969**

Typ	Artikelnummer
Spare part	ERS VAGG 6-63 10.01.27.01456
Vacuum pump	EVE-OG 10 AC3 10.03.02.00111
Set of parts subject to wear pump	VST EVE-OG-10 10.03.02.00114
Oil	OEL EVE-OG 1L ANDEROL 555 27.02.01.00055
Sieve insert	SIEB-EINS 18x 32 VAGG 10.01.27.01993
Pipe (machined)	ROHR 40x3x90 VC-SYS 10.01.27.00471
Horn	HUPE 42.5x43.5 S017 SW 21.05.05.00059

