


Needle gripper

SNG-DL 1.2 24



Art.-Nr.: 10.01.29.00011



Technical data

Attribute	Value
Number of needles	24
Needle diameter	1.2 mm
Pressure range (operating pressure) [bar]	3.0 ... 10.0 bar
Needle stroke Z(NA)	17.5 mm


SNG-DL 1.2 24

Needle gripper SNG-DL is delivered assembled. The assembly consists of:

- gripper of type SNG-DL - available with various needle diameters

Available spare parts: needle module

Available accessories: mounting plate



Design data

Attribute	Value
Length L	263.50 mm
Width B	55.00 mm
Height H	117.00 mm
Thread G1	M5-F
Hole spacing Y1	20.0 mm
Hole spacing X1	20.0 mm
Thread G4	M4-F

Design data SNG-DL 1.2 24



WWW.SCHMALZ.COM/10.01.29.00011

Needle gripper

SNG-DL 1.2 24



Art.-Nr.: 10.01.29.00011



Technical data

Attribute	Value
Weight	1,500.0 g
Installation position	BEL
Number of needles	24
Needle diameter	1.2 mm
Pressure range (operating pressure) [bar]	3.0 ... 10.0 bar
Operating temperature	5 ... 60 °C



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.29.00011



Ordering Data Accessories 10.01.29.00011

Typ		Item number
Mounting plate	BEF-PL 31x34x11.5 G1/4-IG SNG	10.01.29.00093
Plug union, straight	STV-GE M5-AG 6	10.08.02.00201
Plug union, elbow	STV-W M5-AG 6	10.08.02.00296
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



Ordering Data Spare Parts 10.01.29.00011

Typ		Item number
Set of spare parts needle gripper	ERS SNG-DL 1.2	10.01.29.00102



WWW.SCHMALZ.COM/10.01.29.00011