



Art.-Nr.: 10.01.29.00403



Technical data

Attribute	Value
Pressure range (operating pressure) [bar]	bar
Utilization design	Needle gripper
Length L	38.00 mm
Width B	15.00 mm
Height H	11.50 mm
Thread G1	G1/4"-F

BEF-PL 38x15x11.5 G1/4-IG SNG



Design data

Attribute	Value
Length L2	20.00 mm
Length L	38.00 mm
Width B	15.00 mm
Height H2	5.00 mm
Height H	11.50 mm
Internal diameter d	5.50 mm
Thread G1	G1/4"-F
Thread length LG1	11.5 mm
Hole spacing X1	29.0 mm

Design data BEF-PL 38x15x11.5 G1/4-IG SNG



Technical data

Attribute	Value
Weight	14.2 g

Mounting plate

BEF-PL 38x15x11.5 G1/4-IG SNG



Art.-Nr.: 10.01.29.00403



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.29.00403



WWW.SCHMALZ.COM/10.01.29.00403