


Art.-Nr.: 10.01.29.00600



SNG-V 10 1.5 V-CH-7 10.5


Needle gripper SNG-V is delivered assembled.

Available spare parts: needle module, gripping surface

Available accessories: mounting plate (BEF-PL), holder system (HTS)

Technical data

Attribute	Value
Number of needles	10
Needle diameter	1.5 mm
Additional function	Var. stroke, center hole
Pressure range (operating pressure) [bar]	3.0 ... 7.0 bar
Needle stroke Z(NA)	7.0 mm



Design data SNG-V 10 1.5 V-CH-7 10.5

Design data

Attribute	Value
Length L	167.00 mm
Width B	37.00 mm
Height H	56.00 mm
Thread G1	M5-F
Hole size d3	10.5 mm
Hole spacing Y1	20.0 mm
Hole spacing Y2	29.0 mm
Hole spacing X1	20.0 mm
Insertion angle W(E)	30.0 °
Needle stroke Z(NA)	7.0 mm



Art.-Nr.: 10.01.29.00600

**Technical data**

Attribute	Value
Weight	289.0 g
Number of needles	10
Needle diameter	1.5 mm
Additional function	Var. stroke, center hole
Pressure range (operating pressure) [bar]	3.0 ... 7.0 bar
Operating temperature	5 ... 60 °C
Product family	SNG-V
Installation position	Any

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.29.00600**Ordering Data Accessories 10.01.29.00600**

Typ		Item number
Mounting plate	BEF-PL 38x15x11.5 G1/4-IG SNG	10.01.29.00403
Mounting plate	BEF-PL 31x34x11.5 G1/4-IG SNG	10.01.29.00093
Holder system	HTS-A2 SNG AP/AE OP	10.01.29.00622
Holder system	HTS-A3 SNG AP/AE OP	10.01.29.00619
Holder system	HPS-SNG 2M6 AP/AE OP	10.01.29.00666
Plug union, elbow	STV-W M5-AG 6	10.08.02.00296

**Ordering Data Spare Parts 10.01.29.00600**

Typ		Item number
Set of spare parts needle gripper	ERS SNG-V-CH 10 1.5 7	10.01.29.00612
Set of spare parts needle gripper	ERS SNG-V-CH 10 1.5 7	10.01.29.00613

