


SD-MOD 4 32x15x35 FG 9 SWGm


Art.-Nr.: 10.01.30.00121



SD-MOD 4 32x15x35 FG 9 SWGm

Technical data

Attribute	Value
Utilization design	Wafer gripper
Length L	32.00 mm
Width B	15.00 mm



Design data SD-MOD 4 32x15x35 FG 9 SWGm

Design data

Attribute	Value
Length L	32.00 mm
Width B2	11.00 mm
Width B	15.00 mm
Height H	35.00 mm
d2	4.1 mm
Internal diameter d	4.00 mm
Spring stroke Z	3.0 mm
Diameter Ds	9.0 mm
Stroke Z	3.00 mm
Thread G4	M4-M



Technical data

Attribute	Value
Weight	10.4 g
Pressure range (operating pressure) [bar]	bar



Suction-/ Absorption module

SD-MOD 4 32x15x35 FG 9 SWGm



Art.-Nr.: 10.01.30.00121



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00121



WWW.SCHMALZ.COM/10.01.30.00121