





## Technical data

| Attribute          | Value    |
|--------------------|----------|
| Length L           | 12.00 mm |
| Outside diameter D | 80.00 mm |
| Size               | ST1      |

FLAN-PL 80x12-ST1



## Design data

| Attribute            | Value    |
|----------------------|----------|
| Length L1            | 15.00 mm |
| Length L2            | 3.00 mm  |
| Length L             | 12.00 mm |
| Outside diameter D2  | 50.0 mm  |
| Outside diameter D   | 80.00 mm |
| Internal diameter d1 | 6.6 mm   |
| Internal diameter d  | 28.00 mm |
| Thread G2            | M4-F     |
| Dmk                  | 46.0 mm  |
| Length L3            | 3.00 mm  |

Design data FLAN-PL 80x12-ST1



## Technical data

| Attribute                                 | Value   |
|-------------------------------------------|---------|
| Weight                                    | 153.0 g |
| Pressure range (operating pressure) [bar] | bar     |

Flange plate (round)

## FLAN-PL 80x12-ST1



Art.-Nr.: 10.01.30.00167



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.30.00167](http://www.schmalz.com/10.01.30.00167)



[WWW.SCHMALZ.COM/10.01.30.00167](http://WWW.SCHMALZ.COM/10.01.30.00167)