



Art.-Nr.: 10.01.30.00191



SWGm-6S W 146x146x65 PEEK

Technical data

Attribute	Value
Material	Polyetheretherketon
Additional function area gripper	wet wafers
Length L	146.00 mm
Width B	146.00 mm
Height H	65.00 mm
Shape	Lateral exhaust air



Design data SWGm-6S W 146x146x65 PEEK

Design data

Attribute	Value
Length L	146.00 mm
Width B	146.00 mm
Height H2	10.50 mm
Height H	65.00 mm
Internal diameter d1	4.5 mm
d2	14.0 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-F
Thread G2	M4-F
Hole spacing X1	46.0 mm



Art.-Nr.: 10.01.30.00191



Technical data

Attribute	Value
Weight	310.0 g
Size	6.00
Pressure range (operating pressure) [bar]	1.0 ... 3.0 bar
Operating temperature	°C
Air consumption	60 ... 120 l/min
Air consumption [m³/h]	m³/h
Suction rate	160 ... 235 l/min
Suction rate [m³/h]	m³/h
Shape	Lateral exhaust air
Product family	SWGm-WET



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00191

