

**Technical data**


Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Height H	27.80 mm

SAUG-SCG 40 NBR-CO-55

The flow gripper SCG for dry food s designed in two parts. In order to receive a complete gripper (flow gripper + suction cup) the following ordering steps are required:

- Flow gripper (step1) – available for axial or sideways mounting
- Suction cup (step 2)

Available accessories: plug-in screw union

**Design data**

Attribute	Value
Height H	27.80 mm
Outside diameter D1	41.0 mm
Nominal diameter dn	18.50 mm
Thread G1	M37x1-F
Thread length LG1	5.0 mm
Spring stroke Z	3.7 mm
Diameter Ds	40.5 mm
Diameter Dmax(S)	41.5 mm
Diameter Dmax(N)	39.6 mm

Design data SAUG-SCG 40 NBR-CO-55

Art.-Nr.: 10.01.30.00718

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Weight	21.2 g
Size	40.00
Number of folds	0.0
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Air consumption	l/min
Air consumption [m³/h]	m³/h
Suction rate	l/min
Suction rate [m³/h]	m³/h
Holding force	N
Product family	SAUG-SCG

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00718

**Discontinued item**

The product family will be discontinued and is available until **01.12.2025**

Starting from this time, the article can no longer be ordered.

alternative article **10.01.30.01085 SAUG-SCG 40 NBR-ESD-55 602 B**

**Ordering Data Accessories 10.01.30.00718**

Typ		Item number
Flow gripper (mod)	SCG 1xE100 A MA AR M37x1-AG	10.01.30.00092
Flow gripper (mod)	SCG 1xE100 A MA SDA M37x1-AG	10.01.30.00359
Flow gripper (mod)	SCG 1xE100 A MS AR M37x1-AG	10.01.30.00170
Flow gripper (mod)	SCG 1xE100 A MS SDA M37x1-AG	10.01.30.00360

