

**Teknik veriler**


Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	30.00

SAUG-SCGS 30 NBR-ESD-55

SCGS akış tutucu iki parçadan oluşmaktadır. Komple bir tutucu (akış tutucu + vantuz) elde etmek için aşağıdaki sipariş adımları gereklidir:

- Akış tutucu (adım1) - yana montaj için mevcuttur
- Vantuz (adım 2)

Mevcut aksesuarlar: vidalı itme bağlantısı

**Tasarım verileri**

Attribute	Value
Yükseklik H	24.10 mm
Dış çap D1	31.0 mm
Nominal çap dn	12.00 mm
Dış G1	M20x1-F
Dış uzunluğu LG1	5.0 mm
Yay stroku Z	2.8 mm
Çap Ds	30.2 mm
Çap Dmax(S)	31.5 mm
Çap Dmax(N)	25.0 mm

Tasarım verileri SAUG-SCGS 30 NBR-ESD-55

Vantuz (yuvarlak)

SAUG-SCGS 30 NBR-ESD-55



Art.-Nr.: 10.01.30.00876



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	30.00
Ürün ailesi	SAUG-SCGS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00876



Discontinued item

The product family will be discontinued and is available until **31.12.2027**
Starting from this time, the article can no longer be ordered.
alternative article **10.01.30.01092 SAUG-SCGS 30 NBR-ESD-55 B**



Yedek parçalar için sipariş verileri 10.01.30.00876

Typ	Ürün numarası
Düz vantuz (yuvarlak)	FLSA 30 NBR-ESD-55
	10.01.06.04214



WWW.SCHMALZ.COM/10.01.30.00876