

**Technical data**


Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	30.00

SAUG-SCGS 30 NBR-ESD-55

The flow gripper SCGS is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

- Flow gripper (step1) – available for sideways mounting
- Suction cup (step 2)

Available accessories: screw in push fitting

**Design data**

Attribute	Value
Height H	24.10 mm
Outside diameter D1	31.0 mm
Nominal diameter dn	12.00 mm
Thread G1	M20x1-F
Thread length LG1	5.0 mm
Spring stroke Z	2.8 mm
Diameter Ds	30.2 mm
Diameter Dmax(S)	31.5 mm
Diameter Dmax(N)	25.0 mm

Design data SAUG-SCGS 30 NBR-ESD-55



Suction cup (round)

SAUG-SCGS 30 NBR-ESD-55



Art.-Nr.: 10.01.30.00876



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	30.00
Product family	SAUG-SCGS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00876



Discontinued item

The product family will be discontinued and is available until **31.12.2027**

Starting from this time, the article can no longer be ordered.

alternative article **10.01.30.01092 SAUG-SCGS 30 NBR-ESD-55 B**



Ordering Data Spare Parts 10.01.30.00876

Typ	Item number
Flat suction cup (round)	FLSA 30 NBR-ESD-55 10.01.06.04214



WWW.SCHMALZ.COM/10.01.30.00876