

Suction cup (round)

SAUG-SCGS 40 NBR-ESD-55 B



Art.-Nr.: 10.01.30.01093



Technical data


Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	40.00

SAUG-SCGS 40 NBR-ESD-55 B

The flow gripper SCGS is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

- Flow gripper (step1) – available for sideways mounting
- Suction cup (step 2)

Available accessories: screw in push fitting



Design data

Attribute	Value
Height H	29.00 mm
Nominal diameter dn	27.00 mm
Thread G1	M20x1-F
Thread length LG1	6.5 mm
Spring stroke Z	6.5 mm
Diameter Ds	39.4 mm
Diameter Dmax(S)	42.0 mm
Diameter Dmax(N)	25.0 mm

Design data SAUG-SCGS 40 NBR-ESD-55 B



WWW.SCHMALZ.COM/10.01.30.01093

Suction cup (round)

SAUG-SCGS 40 NBR-ESD-55 B



Art.-Nr.: 10.01.30.01093



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Weight	26.0 g
Size	40.00
Product family	SAUG-SCGS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.01093



Ordering Data Spare Parts 10.01.30.01093

Typ	Item number
Bellows suction cup f SCG(S)-gripper BCG 40 NBR-ESD-55 SC095	10.01.06.04575



WWW.SCHMALZ.COM/10.01.30.01093