

Suction cup (round)

SAUG-SCGS 20 SI-HD-65 602 B



Art.-Nr.: 10.01.30.01103



Technical data


Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	20.00

SAUG-SCGS 20 SI-HD-65 602 B

The flow gripper SCGS is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

- Flow gripper (step1) – available for sideways mounting
- Suction cup (step 2)

Available accessories: screw in push fitting



Design data

Attribute	Value
Height H	22.50 mm
Nominal diameter dn	15.00 mm
Thread G1	M20x1-F
Thread length LG1	5.0 mm
Spring stroke Z	3.0 mm
Diameter Ds	21.5 mm
Diameter Dmax(S)	25.0 mm
Diameter Dmax(N)	25.0 mm

Design data SAUG-SCGS 20 SI-HD-65 602 B



WWW.SCHMALZ.COM/10.01.30.01103

Suction cup (round)

SAUG-SCGS 20 SI-HD-65 602 B



Art.-Nr.: 10.01.30.01103



Technical data

Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Weight	9.4 g
Size	20.00
Product family	SAUG-SCGS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.01103



Ordering Data Spare Parts 10.01.30.01103

Typ	Item number
Bellows suction cup f SCG(S)-gripper BCG 20 SI-HD-65 SC085	10.01.06.04845



WWW.SCHMALZ.COM/10.01.30.01103