

Suction cup (round)

SAUG-SFG 30 SI-HD-65 B



Art.-Nr.: 10.01.30.01143



Technical data

Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	30.00
Height H	36.30 mm


SAUG-SFG 30 SI-HD-65 B

The flow gripper SFG is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

Flow gripper (step 1) - available for side mounting

Suction cups (step 2)

Available spare parts: Flat suction cups FLSA



Design data

Attribute	Value
Length L	36.00 mm
Width B	25.00 mm
Height H	36.30 mm
Internal diameter d	12.50 mm
Spring stroke Z	5.5 mm
Diameter Ds	29.5 mm
Diameter Dmax(S)	32.5 mm

Design data SAUG-SFG 30 SI-HD-65 B



WWW.SCHMALZ.COM/10.01.30.01143

Suction cup (round)

SAUG-SFG 30 SI-HD-65 B



Art.-Nr.: 10.01.30.01143



Technical data

Attribute	Value
Suction cup material	Silicone SI-HD



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.01143



Ordering Data Spare Parts 10.01.30.01143

Typ	Item number
Bellows suction cup f SCG(S)-gripper BCG 30 SI-HD-65 SC085	10.01.06.04846



WWW.SCHMALZ.COM/10.01.30.01143