

Suction cup (round)

## SAUG-SFG 40 SI-HD-65 B



Art.-Nr.: 10.01.30.01145



### Technical data

| Attribute                   | Value          |
|-----------------------------|----------------|
| Suction cup material        | Silicone SI-HD |
| Material hardness [Shore A] | 65.0 Shore A   |
| Size                        | 40.00          |
| Height H                    | 29.50 mm       |


SAUG-SFG 40 SI-HD-65 B

The flow gripper SFG is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

Flow gripper (step 1) - available for side mounting

Suction cups (step 2)

Available spare parts: Flat suction cups FLSA



### Design data

| Attribute           | Value    |
|---------------------|----------|
| Length L            | 36.00 mm |
| Width B             | 25.00 mm |
| Height H            | 29.50 mm |
| Internal diameter d | 17.40 mm |
| Spring stroke Z     | 6.5 mm   |
| Diameter Ds         | 39.4 mm  |
| Diameter Dmax(S)    | 42.0 mm  |

Design data SAUG-SFG 40 SI-HD-65 B



[WWW.SCHMALZ.COM/10.01.30.01145](http://WWW.SCHMALZ.COM/10.01.30.01145)

Suction cup (round)

## SAUG-SFG 40 SI-HD-65 B



Art.-Nr.: 10.01.30.01145



### Technical data

| Attribute            | Value          |
|----------------------|----------------|
| Suction cup material | Silicone SI-HD |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.30.01145](http://www.schmalz.com/10.01.30.01145)



### Ordering Data Spare Parts 10.01.30.01145

| Typ                                                        | Item number    |
|------------------------------------------------------------|----------------|
| Bellows suction cup f SCG(S)-gripper BCG 40 SI-HD-65 SC095 | 10.01.06.04847 |



[WWW.SCHMALZ.COM/10.01.30.01145](http://WWW.SCHMALZ.COM/10.01.30.01145)