

Suction cup (round)

SAUG-SFG 40 SI-MD-55 B

Art.-Nr.: 10.01.30.01146



Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Height H	29.50 mm


SAUG-SFG 40 SI-MD-55 B

The flow gripper SFG is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

Flow gripper (step 1) - available for side mounting

Suction cups (step 2)

Available spare parts: Flat suction cups FLSA



Design data

Attribute	Value
Length L	36.00 mm
Width B	25.00 mm
Height H	29.50 mm
Internal diameter d	17.40 mm
Spring stroke Z	6.5 mm
Diameter Ds	39.4 mm
Diameter Dmax(S)	42.0 mm

Design data SAUG-SFG 40 SI-MD-55 B



WWW.SCHMALZ.COM/10.01.30.01146

Suction cup (round)

SAUG-SFG 40 SI-MD-55 B



Art.-Nr.: 10.01.30.01146



Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.01146



Ordering Data Spare Parts 10.01.30.01146

Typ	Item number
Bellows suction cup f SCG(S)-gripper BCG 40 SI-MD-55 SC095	10.01.06.04560



WWW.SCHMALZ.COM/10.01.30.01146