


Art.-Nr.: 10.01.36.00065

**Technical data**

Attribute	Value
Nominal flow rate	60.000 m ³ /h
Length L1	65.00 mm
Outside diameter D1	55.0 mm
Dmk	46.0 mm

VEE-RU 55x65 60 FL

**Design data**

Attribute	Value
Length L1	65.00 mm
Length L	65.00 mm
Outside diameter D1	55.0 mm
Outside diameter D2	25.0 mm
Thread G1	G1/8"-F
Thread G2	M4-M
Thread length LG2	7.7 mm
Dmk	46.0 mm

Design data VEE-RU 55x65 60 FL

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00065WWW.SCHMALZ.COM/10.01.36.00065

Art.-Nr.: 10.01.36.00065



Ordering Data Accessories 10.01.36.00065

Typ		Item number
Suction cup	RFBP 50 50 BA SPB2	10.01.45.00096
Suction cup	RFBP 100 58 BA SPB2	10.01.45.00091
Suction cup	RFBP 100 58 BA O10	10.01.45.00092
Suction cup	RFBP 120 120 BA SPB2	10.01.45.00085
Suction cup	RFBP 120 120 BA O10	10.01.45.00086

