



Art.-Nr.: 10.01.36.00121

**Technical data**

Attribute	Value
Flow rate max.	60.000 m ³ /h
Length L1	32.00 mm
Dmk	46.0 mm
Number of holes	8

VEE-QCM 32

Flange module VEE-QCM is delivered as a ready to connect product.

**Design data**

Attribute	Value
Length L1	32.00 mm
Length L	19.00 mm
Outside diameter D1	55.0 mm
Outside diameter D	25.40 mm
Internal diameter d	4.50 mm
Thread G2	M4-M
Thread length LG2	8.6 mm
Dmk	46.0 mm

Design data VEE-QCM 32

**Technical data**

Attribute	Value
Connection	Bayonet connection



Flange module
VEE-QCM 32



Art.-Nr.: 10.01.36.00121



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00121



Ordering Data Accessories 10.01.36.00121

Typ		Item number
CobotPump	ECBPi 12 24V-DC M12-8	10.03.01.00314
CobotPump	ECBPi 12 24V-DC TB-8	10.03.01.00364
Suction cup	RFBP 50 50 BA SPB2	10.01.45.00096
Suction cup	RFBP 100 58 BA SPB2	10.01.45.00091
Suction cup	RFBP 100 58 BA O10	10.01.45.00092
Suction cup	RFBP 120 120 BA SPB2	10.01.45.00085
Suction cup	RFBP 120 120 BA O10	10.01.45.00086



WWW.SCHMALZ.COM/10.01.36.00121