

Flange module

VEE-QCM 67



Art.-Nr.: 10.01.36.00123




VEE-QCM 67

Flange module VEE-QCM is delivered as a ready to connect product.

Technical data

Attribute	Value
Flow rate max.	60.000 m ³ /h
Length L1	67.00 mm
Thread G1	G1/8"-F
Dmk	46.0 mm
Number of holes	8



Design data VEE-QCM 67

Design data

Attribute	Value
Length L1	67.00 mm
Length L	54.00 mm
Outside diameter D1	55.0 mm
Outside diameter D2	25.0 mm
Outside diameter D	25.40 mm
Thread G1	G1/8"-F
Thread G2	M4-M
Thread length LG2	8.6 mm
Dmk	46.0 mm



Technical data

Attribute	Value
Connection	Bayonet connection



Flange module
VEE-QCM 67



Art.-Nr.: 10.01.36.00123



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00123



Ordering Data Accessories 10.01.36.00123

Typ		Item number
Solenoid valve pressure	EMV 1.5 24V-DC 3/2 NC K-2P	10.05.01.00288
Flange plate (round)	FLAN-PL 55x7.5-AB1	10.01.30.00015
Flange plate (round)	FLAN-PL 55x7.5-EL1	10.01.30.00208
Flange plate (round)	FLAN-PL 55x9.5-JP1	10.01.30.00194
Flange plate (round)	FLAN-PL 63x10.5-AD1	10.01.30.00016
Flange plate (round)	FLAN-PL 63x11.5-UNI	10.01.30.00017
Flange plate (round)	FLAN-PL 80x12-ST1	10.01.30.00167
Suction cup	RFBP 50 50 BA SPB2	10.01.45.00096
Suction cup	RFBP 100 58 BA SPB2	10.01.45.00091
Suction cup	RFBP 100 58 BA O10	10.01.45.00092
Suction cup	RFBP 120 120 BA SPB2	10.01.45.00085
Suction cup	RFBP 120 120 BA O10	10.01.45.00086



WWW.SCHMALZ.COM/10.01.36.00123