

VEE-FE-A 20

Art.-Nr.: 10.01.36.00132



VEE-FE-A 20

Technical data

Attribute	Value
Flow rate max.	20.000 m³/h

Design data VEE-FE-A 20

Design data

Attribute	Value
Length L	21.00 mm
Width B	60.00 mm
Height H1	82.50 mm
Outside diameter D	55.00 mm
Internal diameter d	4.50 mm
Dmk	46.0 mm



Technical data

Attribute	Value
Weight	104.0 g
Flow rate max.	20.000 m³/h
Operating temperature	-25 ... 80 °C
Operating temperature min.	-25.0 °C
Operating temperature max.	80.0 °C



Adapter for flange extension

VEE-FE-A 20



Art.-Nr.: 10.01.36.00132



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00132



WWW.SCHMALZ.COM/10.01.36.00132