

Art.-Nr.: 10.01.36.00133



VEE-FE-A 60

Technical data

Attribute	Value
Flow rate max.	60.000 m ³ /h

Design data

Attribute	Value
Length L	35.00 mm
Width B	60.00 mm
Height H1	79.50 mm
Outside diameter D	55.00 mm
Internal diameter d	4.50 mm
Dmk	46.0 mm

Design data VEE-FE-A 60



Technical data

Attribute	Value
Weight	107.0 g
Flow rate max.	60.000 m ³ /h
Operating temperature	-25 ... 80 °C
Operating temperature min.	-25.0 °C
Operating temperature max.	80.0 °C



Adapter for flange extension

VEE-FE-A 60



Art.-Nr.: 10.01.36.00133



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00133



WWW.SCHMALZ.COM/10.01.36.00133