


Art.-Nr.: 10.01.36.00200



VEE-QCMV HF 2 13 22

Technical data

Attribute	Value
Number of stages	2
Shape	High flow



Design data VEE-QCMV HF 2 13 22

Design data

Attribute	Value
Length L2	91.80 mm
Length L	144.60 mm
Width B	55.00 mm
Height H1	67.00 mm
Height H	51.90 mm
Outside diameter D	25.40 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-F
Thread G2	M4-M
Thread length LG2	8.6 mm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.36.00200WWW.SCHMALZ.COM/10.01.36.00200

Art.-Nr.: 10.01.36.00200

**Ordering Data Accessories 10.01.36.00200**

Typ		Item number
Solenoid valve pressure	EMV 1.5 24V-DC 3/2 NC K-2P	10.05.01.00288
Flange plate (round)	FLAN-PL 55x7.5-AB1	10.01.30.00015
Flange plate (round)	FLAN-PL 55x7.5-EL1	10.01.30.00208
Flange plate (round)	FLAN-PL 55x9.5-JP1	10.01.30.00194
Flange plate (round)	FLAN-PL 63x10.5-AD1	10.01.30.00016
Flange plate (round)	FLAN-PL 63x11.5-UNI	10.01.30.00017
Flange plate (round)	FLAN-PL 80x12-ST1	10.01.30.00167
Suction cup	RFBP 50 50 BA SPB2	10.01.45.00096
Suction cup	RFBP 100 58 BA SPB2	10.01.45.00091
Suction cup	RFBP 100 58 BA O10	10.01.45.00092
Suction cup	RFBP 120 120 BA SPB2	10.01.45.00085
Suction cup	RFBP 120 120 BA O10	10.01.45.00086

**Ordering Data Spare Parts 10.01.36.00200**

Typ		Item number
Ejector module	SEP HF 2 13 22	10.02.01.01347
Schmalz Holder Cap	SHC 2 22	10.02.01.01430

