

Art.-Nr.: 10.01.38.00963



FXP-S-SVK 442 5R36 SPB2-20-P F

**Technical data**


|                                  |                                    |
|----------------------------------|------------------------------------|
| Construction vacuum switch       | PNP switching                      |
| Weight                           | 3.600 kg                           |
| Voltage DC                       | 24 V - DC                          |
| Air consumption [l/min]          | 250.0 l/min                        |
| Design vacuum generator          | Multi-stage ejector SEMP           |
| Additional function area gripper | 1x control valve vacuum / blow-off |
| Number of suction cells          | 55                                 |
| Length L                         | 442.00 mm                          |
| Width B                          | 130.00 mm                          |
| Product family                   | FXP                                |
| Arrangement                      | 5R36                               |

- Integrated control valves at FXP-S (optional)
- Control of vacuum on/off (24V DC, normally open) and blow off on/off (24V DC, normally closed) on version FXP-S
- Integrated in the end cover
- Electrical connection: M12 plug (4-pole)

Available spare parts: sealing foam (DI-PL), suction cup (SPB2)



Art.-Nr.: 10.01.38.00963

**Design data**

|                 |           |
|-----------------|-----------|
| Length L2       | 402.00 mm |
| Length L        | 442.00 mm |
| Width B         | 130.00 mm |
| Height H1       | 122.00 mm |
| Height H2       | 33.00 mm  |
| Height H        | 83.00 mm  |
| Length L3       | 154.00 mm |
| Width B3        | 21.60 mm  |
| Height H3       | 7.70 mm   |
| Height H4       | 5.50 mm   |
| Hole spacing Y1 | 90.0 mm   |
| Valve type      | SVK       |
| Height H5       | 28.00 mm  |

Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3 Note: Two ejectors and silencer box covers are used for the 1,234 mm and 1,432 mm lengths. Type FXP requires compressed air hose 12/9 mm.

Design data FXP-S-SVK 442 5R36 SPB2-20-P F

**Technical data**

|                                  |                                    |
|----------------------------------|------------------------------------|
| Weight                           | 3.600 kg                           |
| Air consumption [l/min]          | 250.0 l/min                        |
| Additional function area gripper | 1x control valve vacuum / blow-off |
| Number of suction cells          | 55                                 |
| Suction rate (max.)              | 1,050.0 l/min                      |
| Product family                   | FXP                                |
| Arrangement                      | 5R36                               |
| Voltage                          | 24V - DC                           |
| with                             | Filter                             |
| Sealing element                  | Suction Cups                       |
| Suction force at -250 mbar       | 180.00 N                           |

Sound level: 74 dB(A) Max. degree of evacuation 55 %



31.12.2027


[WWW.SCHMALZ.COM/10.01.38.00963](http://WWW.SCHMALZ.COM/10.01.38.00963)

Art.-Nr.: 10.01.38.00963

**Ordering Data Accessories 10.01.38.00963**

| Typ                      |                                   | Item number    |
|--------------------------|-----------------------------------|----------------|
| Flange plate             | FLAN-PL 120x85x10 ST FLGR         | 10.01.10.05701 |
| Flexolink                | FLK G1/2-IG G1/2-AG               | 10.01.03.00175 |
| Suspension, flexible     | FST-FLEX 25 HD1 G1/2-AG G3/8-IG   | 10.01.10.05697 |
| Suspension, flexible     | FST-FLEX 25 HD2 G1/2-AG G3/8-IG   | 10.01.10.05695 |
| Suspension, flexible     | FST-FLEX 50 HD1 G1/2-AG G3/8-IG   | 10.01.10.05687 |
| Suspension, flexible     | FST-FLEX 50 HD2 G1/2-AG G3/8-IG   | 10.01.10.05168 |
| Suspension, flexible     | FST-FLEX 75 HD1 G1/2-AG G3/8-IG   | 10.01.10.05698 |
| Suspension, flexible     | FST-FLEX 75 HD2 G1/2-AG G3/8-IG   | 10.01.10.05696 |
| Suspension, rigid        | FST-STARR 25 HD1 G1/2-AG G3/8-IG  | 10.01.10.05810 |
| Suspension, rigid        | FST-STARR 25 HD2 G1/2-AG G3/8-IG  | 10.01.10.05806 |
| Suspension, rigid        | FST-STARR 50 HD1 G1/2-AG G3/8-IG  | 10.01.10.05809 |
| Suspension, rigid        | FST-STARR 50 HD2 G1/2-AG G3/8-IG  | 10.01.10.05805 |
| Suspension, rigid        | FST-STARR 75 HD1 G1/2-AG G3/8-IG  | 10.01.10.05808 |
| Suspension, rigid        | FST-STARR 75 HD2 G1/2-AG G3/8-IG  | 10.01.10.05803 |
| Flange module            | MOD-FLAN 120x120 FXP-FMP          | 10.01.21.00244 |
| Flange module            | MOD-FLAN 176.6x118 FXP            | 10.01.38.01722 |
| Vacuum switch (inst)     | VS-MONT 84x21x34.5 VSi-V FXP      | 10.01.38.02691 |
| Mounting set reed switch | SET fuer-Sensor(FXP/FMP)          | 10.01.38.01194 |
| Mounting set             | SET FXC-FMC                       | 10.01.21.01291 |
| Mounting set             | SET FXP-FMP                       | 10.01.21.02407 |
| Mounting set             | SET FXP-FMP 4NUTSTEIN G20         | 10.01.21.00243 |
| Vacuum gauge             | VAM 40 V U BAR                    | 10.07.02.00046 |
| Vacuum hose (meter)      | VSL 12-9 PU MI-TR                 | 10.07.09.00037 |
| Sliding block            | NUT-STEI 20x20 M8-IG 10           | 25.09.06.00012 |
| Sliding block            | NUT-STEI 20x20 M6-IG 10           | 25.09.06.00036 |
| Cover (complex)          | ABDK-PROF-10x7x1450-KU-SW-FXP-FMP | 26.07.03.00002 |
| Connection cable         | ASK B-M12-5 5000 K-5P             | 21.04.05.00080 |
| Flange plate             | FLAN-PL 120x120x10 FXC-FMC        | 10.01.21.00313 |
| Flexolink                | FLK G1/2-IG G1/2-AG V             | 10.01.03.00207 |
| Vacuum switch (inst)     | VS-MONT 76.5x19 VSi FXP-FMP       | 10.01.38.02485 |

**Ordering Data Spare Parts 10.01.38.00963**

| Typ                          |                               | Item number    |
|------------------------------|-------------------------------|----------------|
| Set of spare parts           | ERS FXP-S-SEMP-50 DECKEL      | 10.01.38.02190 |
| Masking foil (glued)         | MASK-FOL SVK 402 5R36 FXP-FMP | 10.01.38.00525 |
| Silencer (cube-shaped-inst.) | SD 120x79x29 FXP              | 10.01.38.01607 |



Area Gripper

# FXP-S-SVK 442 5R36 SPB2-20-P F



Art.-Nr.: 10.01.38.00963



Ordering Data Wear Parts 10.01.38.00963

| Typ                         |                   | Item number    |
|-----------------------------|-------------------|----------------|
| Bellows suction cup (round) | SPB2 20 SI-40 P F | 10.01.38.00465 |



[WWW.SCHMALZ.COM/10.01.38.00963](http://WWW.SCHMALZ.COM/10.01.38.00963)