


Art.-Nr.: 10.01.38.03470



Technical data

Attribute	Value
Weight	6.500 kg
Shape fittings	Straight
Max. air consumption blow-off	800.0 l/min
Additional function area gripper	1x control valve vacuum / blow-off
Length L	1,036.00 mm
Width B	130.00 mm
Outside diameter D	60.00 mm
Product family	FMP
Arrangement	3R54


FMP-S-SVK 1036 3R54 SPB2-40-P G60

- Integrated control valves at FMP-S (optional)
- Control of vacuum on/off (24V DC, normally open) and blow off on/off (24V DC, normally closed), as well as hose accumulator preload and blower ventilation function with version FMP-S
- Integrated in the end cover
- Electrical connection: M12 plug (4-pole)

Available spare parts: sealing foam (DI-PL), suction cup (SPB2)



Art.-Nr.: 10.01.38.03470

**Design data**

Attribute	Value
Length L2	996.00 mm
Length L	1,036.00 mm
Width B	130.00 mm
Height H1	150.40 mm
Height H2	55.00 mm
Height H	104.80 mm
Outside diameter D	60.00 mm
Length L3	77.00 mm
Width B3	21.60 mm
Height H3	7.70 mm
Height H4	5.50 mm
Hole spacing Y1	90.0 mm
Valve type	SVK
Height H5	46.00 mm

Note: Vacuum hose with internal diameter equal to dimension D required. See Technical Data -> Shape

Design data FMP-S-SVK 1036 3R54 SPB2-40-P G60

**Technical data**

Attribute	Value
Electrical connection	Male connect M12, 4 pol
Weight	6.500 kg
Number of suction cells	56
Additional function area gripper	1x control valve vacuum / blow-off
Required suction capacity for $p_u = -0.25$ bar	750.0 l/min
Product family	FMP
Arrangement	3R54
Voltage	24V - DC
Sealing element	Suction Cups
Suction force at -250 mbar	600.00 N

Note: Air consumption: At a compressed air inlet pressure of 5.5 bar / Suction force: At a vacuum of -0.25 bar and with the gripper fully loaded with a workpiece typical for this application (wooden board with a textured surface) / Required suction capacity: The external vacuum generator used must provide at least the specified suction volume (at the FMP's vacuum connection piece) at a vacuum of -0.25 bar, but no more than 135% of the specified suction volume

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.38.03470


WWW.SCHMALZ.COM/10.01.38.03470

Art.-Nr.: 10.01.38.03470

**Discontinued item**

The product family will be discontinued and is available until **31.12.2027**
Starting from this time, the article can no longer be ordered.
alternative article

**Ordering Data Accessories 10.01.38.03470**

Typ		Item number
Hose connector, straight (inst)	SCHL-AN 60-79x79x45 FMP-S	10.01.38.03582
Hose connector, bent (inst)	SCHL-AN W 60-79x79x45 FMP-S	10.01.38.03983
Sealing plate (inst)	VRS-PL 79x79x12 SPZ G2-IG	10.01.21.01280

**Ordering Data Spare Parts 10.01.38.03470**

Typ		Item number
Building group Solenoid valve	VENT-BGR FMP-S-50	10.01.38.03682

**Ordering Data Wear Parts 10.01.38.03470**

Typ		Item number
Bellows suction cup (round)	SPB2 40 SI-55 P	10.01.06.03126

