

Sealing plate (inst)

DI-PL 1234-3R18 O10O10 F FXP-/FMP-i



Art.-Nr.: 10.01.38.07319



Technical data

Attribute	Value
Weight	0.100 kg
Additional function area gripper	Filter
Measuring range [bar]	bar
Utilization design	Vacuum area gripping system FXP-i/ FMP-i
Length L	1,234.00 mm
Width B	128.00 mm
Height H	20.00 mm
Arrangement suction cells	3 rows, 18 mm

DI-PL 1234-3R18 O10O10 F FXP-/FMP-i

Design data

Attribute	Value
-----------	-------

Design data DI-PL 1234-3R18 O10O10 F FXP-/FMP-i



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.38.07319



WWW.SCHMALZ.COM/10.01.38.07319