

Art.-Nr.: 10.01.40.00189



FMHD 1260x170 2R28 O20 G60


The area gripping system FMHD is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Weight	19.600 kg
Shape fittings	Pillar straight, Ø 60
Material type	Foam O, Height 20 mm
Length L	1,260.00 mm
Width B	170.00 mm
Arrangement suction cells	2 rows, 28 mm

Design data

Attribute	Value
Length L1	1,267.80 mm
Length L2	75.00 mm
Length L	1,260.00 mm
Width B1	191.50 mm
Width B2	175.50 mm
Width B	170.00 mm
Height H1	158.70 mm
Height H2	20.00 mm
Height H	111.70 mm
Outside diameter D	60.00 mm



Design data FMHD 1260x170 2R28 O20 G60



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.40.00189



WWW.SCHMALZ.COM/10.01.40.00189

Art.-Nr.: 10.01.40.00189

**Ordering Data Accessories 10.01.40.00189**

Typ		Item number
Suspension, rigid	FST-STARR 25 HD2 G1/2-AG G3/8-IG	10.01.10.07012
Suspension, rigid	FST-STARR 50 HD2 G1/2-AG G3/8-IG	10.01.10.07013
Suspension, rigid	FST-STARR 75 HD2 G1/2-AG G3/8-IG	10.01.10.07014
Suspension, flexible	FST-FLEX 25 HD2 G1/2-AG G3/8-IG	10.01.10.07018
Suspension, flexible	FST-FLEX 50 HD2 G1/2-AG G3/8-IG	10.01.10.07019
Suspension, flexible	FST-FLEX 75 HD2 G1/2-AG G3/8-IG	10.01.10.07020
Flexolink	FLK G1/2-IG G1/2-AG	10.01.03.00175
Flexolink	FLK G1/2-IG G1/2-AG V	10.01.03.00207
Flange plate	FLAN-PL 160x120x10 FMHD	10.01.10.08805
Suspension, fixable	FST-C 100-HD1	10.01.20.01260
Flange module	MOD-FLAN 157x120 FMHD	10.01.11.03187
Vacuum distributor	VTR-SL 3x RST60	10.01.10.02779
Vacuum distributor	VTR-SL 4x RST60	10.01.10.03196
Vacuum distributor	VTR-SL 5x RST60	10.01.10.03066
Vacuum/pressure switch	VSi V D M12-4	10.06.02.00580
Connection cable	ASK B-M12-4 5000 K-4P	21.04.05.00263
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Vacuum switch (inst)	VS-MONT 85x21x30.8 VSi SPZ	10.01.22.04338
Sliding block	NUT-STEI 55x20 M3-IG	10.01.21.04651



Art.-Nr.: 10.01.40.00189

**Ordering Data Spare Parts 10.01.40.00189**

Typ		Item number
Sealing plate (FMHD)	DI-PL 1213.4x125 2R28 O04 KE	10.01.40.00103
Sealing plate (FMHD)	DI-PL 1214x168 2R28 O20 KE	10.01.40.01002
Housing cover (cube-shaped-inst.)	GEH-DECK 170x45.5x91.7 NC FMHD	10.01.40.00021
Housing cover (cube-shaped-inst.)	GEH-DECK 170x22.5x91.7 IMP FMHD	10.01.40.00754
Housing cover (cube-shaped-inst.)	GEH-DECK 170x45.5x91.7 NC FMHD	10.01.40.00865
Form seal	DI-FORM 168.2x85.7x2	10.01.40.00013
Solenoid valve	EMV 1.1 24V-DC 3/2 NC H	10.05.01.00277
Sealing plate (FMHD)	DI-PL 52.3x41.6 ZEL PU	10.01.40.00080
Housing cover (cube-shaped-inst.)	GEH-DECK 170x36.5x91.7 FMHD	10.01.40.00024
Housing cover (cube-shaped-inst.)	GEH-DECK 170x36.5x91.7 FMHD	10.01.40.00752
Form seal	DI-FORM 168.2x85.9x2	10.01.40.00014
Cylinder (inst.)	ZYL KURZ-ZYL 40x15 FMHD	10.01.40.00161
Cylinder (inst.)	ZYL KOMP-ZYL 40x15 FMHD	10.01.40.00800
Sealing plate (FMHD)	DI-PL 91x114 ZEL PU	10.01.40.00150
Sealing plate (FMHD)	DI-PL 120x84 ZEL PU	10.01.40.00797
Form seal	DI-FORM 88x88x2	10.01.40.00017
Sealing plate (FMHD)	DI-PL 82.6x82.6 ZEL PU	10.01.40.00799
Mounting set	SET FLGR	10.01.40.00023
Vacuum gauge	VAM 40 V DR BAR	10.01.40.00094
Quick release valve	SEV 4/2	10.05.03.00321
Ball	KUG 8.2 5401 A2 G100	10.01.40.00102
Masking foil	MASK-FOL-3000x40x0.19-9.5-FMHD	10.01.40.00108
Sealing ring (f. screwing)	DR M6 9.5/6.5x1 PA	10.07.08.00017
Sleeve	HUEL 10-6.2x7-FMHD	10.01.40.00151

