

Art.-Nr.: 10.01.41.00017

**Technical data**


Attribute	Value
Material hardness [Shore A]	60.0 Shore A
Connection	M4-IG
Height H1	71.80 mm
Dmk	30.0 mm
Suction cup type	Bellows suction cups SAB
Function suction cup	Centrally fixed pins
Material	NBR
Material workpiece support	NBR
Working area [mm]	60.7 ... 66.5

SSCB-30 60.7-66.5 ZP M4-IG SAB-NBR

The Suction Cup Balance SSCB is delivered assembled. The delivery consists of:

- Suction Cup Balance made of aluminium; with positioning pins
- Suction cups FSG-VU1 or SAB-NBR

Available spare parts: Suction cups (spare parts set), cover cap

**Design data**

Attribute	Value
Height H1	71.80 mm
Outside diameter D1	66.0 mm
Thread G1	M4-F
Thread G2	M3-M
Dmk	30.0 mm
Stroke Z	8.00 mm
Operating height EH (min.)	60.70 mm
Operating height EH (max.)	66.50 mm
Suction stroke Zs	5.8 mm

Design data SSCB-30 60.7-66.5 ZP M4-IG SAB-NBR



Art.-Nr.: 10.01.41.00017



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Weight	200.0 g
Size	22.00



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.41.00017

