

Art.-Nr.: 10.01.42.00013




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Boyut	80.00
Körük Sayısı	1.5
Bađlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAXB 80 ED-85 G1/4-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bađlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	50.00 mm
Dış çap D1	54.1 mm
Dış G1	G1/4"-M
Dış uzunluđu LG1	10.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	22.2 mm
Çap Ds	81.0 mm
Çap Dmax(S)	91.0 mm

Tasarım verileri SAXB 80 ED-85 G1/4-AG

Art.-Nr.: 10.01.42.00013

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	6.0 mm
İř parası yarıapı dak (dışbükey)	32.5 mm
Emme kuvveti (-600mbar)	150.00 N
Ağırlık	47.2 g
Yanal kuvvet	176.0 N
Yanal kuvvet yağlı yüzey	155.0 N
Cilt	70.700 cm ³
Boyut	80.00
Körük Sayısı	1.5
Bađlantı	G1/4"-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00013

WWW.SCHMALZ.COM/10.01.42.00013