


Art.-Nr.: 10.01.42.00015



SAXB 80 ED-85 M10-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri SAXB 80 ED-85 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	80.00
Körük Sayısı	1.5
Bağlantı	M10-AG
Meme ucu malzemesi	Çelik

Tasarım verileri

Attribute	Value
Yükseklik H	50.00 mm
Dış çap D1	54.1 mm
Dış G1	M10-M
Dış uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	22.2 mm
Çap Ds	81.0 mm
Çap Dmax(S)	91.0 mm

Bellows suction cups (round)

SAXB 80 ED-85 M10-AG



Art.-Nr.: 10.01.42.00015



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	32.5 mm
Emme kuvveti (-600mbar)	150.00 N
Ağırlık	65.0 g
Yanal kuvvet	176.0 N
Yanal kuvvet yağlı yüzey	155.0 N
Cilt	70.700 cm ³
Boyut	80.00
Körük Sayısı	1.5
Bađlantı	M10-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00015



WWW.SCHMALZ.COM/10.01.42.00015