

Körüklü vantuzlar (yuvarlak)
SAXB 80 ED-85 RA



Art.-Nr.: 10.01.42.00017




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	80,00
Körük Sayısı	1,5
Bağlantı	RA
Meme ucu malzemesi	Alüminyum

SAXB 80 ED-85 RA

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipeli ile birlikte tedarik edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	54,70 mm
Dış çap D1	54,1 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	22,2 mm
Çap Ds	81,0 mm
Uzunluk L4	31,80 mm
Çap Dmax(S)	91,0 mm

Tasarım verileri SAXB 80 ED-85 RA



WWW.SCHMALZ.COM/10.01.42.00017

Körüklü vantuzlar (yuvarlak)
SAXB 80 ED-85 RA



Art.-Nr.: 10.01.42.00017



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	32,5 mm
Emme kuvveti (-600mbar)	150,00 N
Ağırlık	54,20 g
Yanal kuvvet	176,0 N
Yanal kuvvet yağlı yüzey	155,0 N
Cilt	70,700 cm ³
Boyut	80,00
Körük Sayısı	1,5
Bağlantı	Rectangular adapter
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00017



WWW.SCHMALZ.COM/10.01.42.00017