

Bellows suction cups (round)
SAXB 60 ED-85 RA



Art.-Nr.: 10.01.42.00025




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	60.00
Körük Sayısı	1.5
Bağlantı	RA
Meme ucu malzemesi	Alüminyum

SAXB 60 ED-85 RA

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipeli ile birlikte tedarik edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	46.00 mm
Dış çap D1	49.4 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	14.5 mm
Çap Ds	59.6 mm
Uzunluk L4	31.80 mm
Çap Dmax(S)	66.0 mm

Tasarım verileri SAXB 60 ED-85 RA



WWW.SCHMALZ.COM/10.01.42.00025

Bellows suction cups (round)
SAXB 60 ED-85 RA



Art.-Nr.: 10.01.42.00025



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	6.0 mm
İř parası yarıapı dak (dışbükey)	30.0 mm
Emme kuvveti (-600mbar)	90.00 N
Ağırlık	45.1 g
Yanal kuvvet	105.0 N
Yanal kuvvet yağlı yüzey	81.0 N
Cilt	31.900 cm ³
Boyut	60.00
Körük Sayısı	1.5
Bađlantı	Rectangular adapter
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00025



WWW.SCHMALZ.COM/10.01.42.00025