

Art.-Nr.: 10.01.42.00028




SAXB 20 ED-85 G1/4-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	20.00
Körük Sayısı	1.5
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAXB 20 ED-85 G1/4-AG

Tasarım verileri

Attribute	Value
Yükseklik H	25.00 mm
Dış çap D1	20.6 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	5.8 mm
Çap Ds	20.4 mm
Çap Dmax(S)	23.5 mm

Art.-Nr.: 10.01.42.00028

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	8.0 mm
Emme kuvveti (-600mbar)	18.00 N
Ağırlık	13.9 g
Yanal kuvvet	13.0 N
Yanal kuvvet yağlı yüzey	9.5 N
Cilt	1.900 cm ³
Boyut	20.00
Körük Sayısı	1.5
Bađlantı	G1/4"-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00028

WWW.SCHMALZ.COM/10.01.42.00028